

Garant**Vernier caliper Vernier 1/50, Measuring range: 200mm****Order data**

Order number	410105 200
GTIN	4062406122164
Item class	40Z

Description**Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper. Better reading due to a colour-contrast scale.

Precision lapped measuring faces.

Thread table: Calipers table

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: \varnothing 1.9

Packaging: Wallet

Calibration: A1

Scale divisions: 0.02 mm

Graduation: 1/50 mm

Graduation: 1/128 in

Jaw length: 50 mm

Technical description

Graduation	1/50 mm
Calibration	A1
Packaging	Wallet
Scale divisions	0.02 mm

Measuring range	0 - 200 mm
Reversible reading	mm / inch
Jaw length	50 mm
Graduation	1/128 in
Standard	DIN 862
Depth gauge	Ø 1.9
Depth gauge available	yes
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Labelling laser-etched Type	018940
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200