

**Garant****Abrasive cap (CER), 150 grit, Abrasive cap Ø, length, form: 1319C****Order data**

Order number	553038 1319C
GTIN	4062406122782
Item class	51E

**Description****Version:**

**Optimised grit bonding** yields very aggressive abrasion and a high material removal rate.

**Ceramic grit (CER)** ideal for working on stainless steels and nickel alloys. High removal rate and cool cut.

**Application:**

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. The **abrasive caps can be replaced quickly and easily** (replace in direction of slots).

**Note:**

Compatible only for use with ground abrasive cap holder No. 553100.

**Technical description**

recommended speed	16000 min <sup>-1</sup>
Abrasive cap length	19 mm
Abrasive cap Ø	13 mm
Shape	C

Grit	150
Product name attribute	150 grit
Type of product	Abrasive cap

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
dry	suitable		