

Garant**Abrasive cap (CER), 150 grit, Abrasive cap Ø, length, form: 1626G****Order data**

Order number	553038 1626G
GTIN	4062046122753
Item class	51E

Description**Version:**

Optimised grit bonding yields very aggressive abrasion and a high material removal rate.

Ceramic grit (CER) ideal for working on stainless steels and nickel alloys. High removal rate and cool cut.

Application:

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. The **abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Note:

Compatible only for use with ground abrasive cap holder No. 553100.

Technical description

recommended speed	12000 min ⁻¹
Abrasive cap Ø	16 mm
Abrasive cap length	26 mm
Shape	G

Grit	150
Product name attribute	150 grit
Type of product	Abrasive cap

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
dry	suitable		