

Garant GRIDLINE

Pull-out shelf 75 kg, 20×20G, Type: 75**Order data**

Order number	932035 75
GTIN	4062406122973
Item class	9GK

Description**Version:**

Pull-out shelf with **100% full extension** 20×20G. Open in front, shell height at sides 46 mm, installation height 75 mm. Without slots to take slotted dividers.

Suitable for:

Auxiliary cabinet 24×28G.

Supplied with:

Pull-out shelves each complete with 1 pair drawer runner rails.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

Not suitable for fitting into mobile cabinets.

Technical description

Usable width	500 mm
Usable depth	500 mm
Usable width in G	20
Drawer usable area in G	20×20
Usable depth in G	20
Application range	Tool cabinet
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg

Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Pull-out shelf