


Garant**Abrasive cap holder, Head Ø, head length, shape: 1015A****Order data**

Order number	553100 1015A
GTIN	4062406123871
Item class	51E

Description**Version:**

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Slotted, resilient rubber body with steel shank.

Application:

Used mostly in tool making for finishing where access is difficult.

Suitable for:

Abrasive caps No. 553035 – 553328.

Technical description

Head Ø	10 mm
maximum speed	45000 min ⁻¹
Shank Ø	3 mm
Head length	15 mm
Type of product	Abrasive cap holders