

Garant GRIDLINE

Base hazardous substance workstation, Width: 1500mm**Order data**

Order number	981120 1500
GTIN	4062406121075
Item class	9GG

Description**Version:**

GridLine Vario workbench consisting of height-adjustable support legs, storage shelf and sheet metal rear panel together with side panels with square holes. Eterlux worktop 50 mm thick, wear-resistant and resistant to oil, grease, weak acids, and alkalis.

Depth = 750 mm

Colour:

Support leg with manual height adjustment, storage shelf and rear panel RAL 7035 light grey, side panel RAL 7016 anthracite **powder-coated**.

Technical description

Height adjustment range	950 - 1100 mm
Width	1500 mm
Depth	750 mm
Material thickness	1 mm
Height adjustment workstation	950-1100 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Type of height adjustment	mechanical

Hoffmann perforated panel grid interval	9×9
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Hazardous substance workstation