

SWISS TOOLS

## Screw-on toolholder left-hand, HSK-T, Shank $\varnothing$ / insert size: 63/12HPmm



### Order data

Order number	320011 63/12HP
GTIN	2050002004672
Item class	36D

### Description

#### Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

### Technical description

Overhang dimension A	70 mm
Shank $\varnothing$	63 mm
Minimum pre-drill $\varnothing D_1$ min	80 mm
Axis tip distance f	45 mm
Spare part	S01
suitable indexable insert	CC.. 1204..
Adapter	HSK-T
Application type	left-hand
Arbor standard	ISO 12164-3
Through-coolant	yes

Shank type	Hollow shank taper
Type of product	Boring bar