

SWISS TOOLS

Screw-on toolholder right-hand, PSC, Shank \varnothing / insert size: 63/12HPmm



Order data

| | |
|--------------|----------------|
| Order number | 320310 63/12HP |
| GTIN | 2050002004788 |
| Item class | 36D |

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

| | |
|---|-------------|
| Minimum pre-drill $\varnothing D_1$ min | 80 mm |
| Overhang dimension A | 65 mm |
| Axis tip distance f | 45 mm |
| Spare part | S01 |
| suitable indexable insert | CC.. 1204.. |
| Shank \varnothing | 63 mm |
| Adapter | PSC |
| Application type | right-hand |
| Arbor standard | ISO 26623-1 |
| Through-coolant | yes |

Type of product

Boring bar