

SWISS TOOLS

Screw-on toolholder right-hand, HSK-T, Shank Ø / insert size: 63/12HPmm



Order data

Order number	320010 63/12HP
GTIN	2050002004665
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Spare part	S01
Overhang dimension A	70 mm
Minimum pre-drill Ø D ₁ min	80 mm
Axis tip distance f	45 mm
Shank Ø	63 mm
suitable indexable insert	CC.. 1204..
Adapter	HSK-T
Application type	right-hand
Arbor standard	ISO 12164-3
Through-coolant	yes

Shank type	Hollow shank taper
Type of product	Boring bar