

SWISS TOOLS

Screw-on toolholder left-hand, PSC, Shank Ø / insert size: 63/12HPmm



Order data

Order number	320311 63/12HP
GTIN	2050002004795
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Shank Ø	63 mm
Spare part	S01
suitable indexable insert	CC.. 1204..
Minimum pre-drill Ø D ₁ min	80 mm
Overhang dimension A	65 mm
Axis tip distance f	45 mm
Adapter	PSC
Application type	left-hand
Arbor standard	ISO 26623-1
Through-coolant	yes

Type of product

Boring bar