

SWISS TOOLS

Screw-on toolholder left-hand, HSK-T, Shank Ø / insert size: 63/11HPmm

Order data

| | |
|--------------|----------------|
| Order number | 320041 63/11HP |
| GTIN | 2050002004719 |
| Item class | 36D |

Description
Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

| | |
|--|-------------|
| Axis tip distance f | 45 mm |
| Minimum pre-drill Ø D ₁ min | 80 mm |
| Shank Ø | 63 mm |
| Spare part | S05 |
| Overhang dimension A | 70 mm |
| suitable indexable insert | DC.. 11T3.. |
| Adapter | HSK-T |
| Application type | left-hand |
| Arbor standard | ISO 12164-3 |
| Through-coolant | yes |

| | |
|-----------------|--------------------|
| Shank type | Hollow shank taper |
| Type of product | Boring bar |