

SWISS TOOLS

Screw-on toolholder left-hand, HSK-T, Shank Ø / insert size: 63/16HPmm



Order data

Order number	320051 63/16HP
GTIN	2050002004733
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.
PSC clamping stud on request.

Technical description

Shank Ø	63 mm
Axis tip distance f	45 mm
Minimum pre-drill Ø D ₁ min	80 mm
Overhang dimension A	70 mm
Spare part	S07
suitable indexable insert	VB.. 1604..
Adapter	HSK-T
Application type	left-hand
Arbor standard	ISO 12164-3
Through-coolant	yes

Shank type	Hollow shank taper
Type of product	Boring bar