

SWISS TOOLS

Screw-on toolholder right-hand, PSC, Shank Ø / insert size: 63/11HPmm



Order data

Order number	320340 63/11HP
GTIN	2050002004825
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.
PSC clamping stud on request.

Technical description

Spare part	S05
Axis tip distance f	45 mm
suitable indexable insert	DC.. 11T3..
Minimum pre-drill Ø D ₁ min	80 mm
Overhang dimension A	65 mm
Shank Ø	63 mm
Adapter	PSC
Application type	right-hand
Arbor standard	ISO 26623-1
Through-coolant	yes

Type of product

Boring bar