

SWISS TOOLS

## Screw-on toolholder left-hand, PSC, Shank Ø / insert size: 63/11HPmm



### Order data

Order number	320331 63/11HP
GTIN	2050002004818
Item class	36D

### Description

#### Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

### Technical description

Spare part	S05
suitable indexable insert	DC.. 11T3..
Shank Ø	63 mm
Minimum pre-drill Ø D <sub>1</sub> min	80 mm
Axis tip distance f	45 mm
Overhang dimension A	65 mm
Adapter	PSC
Application type	left-hand
Arbor standard	ISO 26623-1
Through-coolant	yes

Type of product

Boring bar