

SWISS TOOLS

Screw-on toolholder neutral, HSK-T, Shank Ø / insert size – A dimension: 6311-130HPmm



Order data

Order number	320070 6311-130HP
GTIN	2050002004757
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.
PSC clamping stud on request.

Technical description

Shank Ø	63 mm
suitable indexable insert	DC.. 11T3..
Overhang dimension A	130 mm
Spare part	S05
Adapter	HSK-T
Application type	neutral
Arbor standard	ISO 12164-3
Through-coolant	yes
Shank type	Hollow shank taper
Type of product	Boring bar

