

SWISS TOOLS

Screw-on toolholder neutral, PSC, Shank Ø / insert size – A dimension: 6316-130HPmm



Order data

Order number	320380 6316-130HP
GTIN	2050002004870
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Shank Ø	63 mm
Spare part	S07
Overhang dimension A	130 mm
suitable indexable insert	VB.. 1604..
Adapter	PSC
Application type	neutral
Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar

