

SWISS TOOLS

Screw-on toolholder neutral, HSK-T, Shank Ø / insert size – A dimension: 6316-130HPmm



Order data

Order number	320080 6316-130HP
GTIN	2050002004771
Item class	36D

Description

Note:

PSC clamping stud on request.

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

Technical description

suitable indexable insert	VB.. 1604..
Spare part	S07
Shank Ø	63 mm
Overhang dimension A	130 mm
Adapter	HSK-T
Application type	neutral
Arbor standard	ISO 12164-3
Through-coolant	yes
Shank type	Hollow shank taper
Type of product	Boring bar

