

**Orbital sander, Type: SPS140****Order data**

Order number	077326 SPS140
GTIN	4002395005826
Item class	03M

Description**Version:****Light-weight and handy 260 W orbital sander:**

- User-friendly hand contact surfaces for even distribution of the pressure.
- DUO fastening system for precise seating of abrasive paper sheets, be they clamp fitting or hook and loop fastener fitting.
- Integral dust extraction through 10-hole abrasive paper.
- Direct connection to dust bag or external dust extraction system.

Supplied with:

Supplied with 4 m power cable, dust bag, punched-out plate, carrying case.

Note:

For suitable abrasive cloth see No. 556980 ff. For suitable hook and loop sanding paper see No. 557620.

Packaging: Carrying case

Power consumption: 260 W

Abrasive paper length (hook and loop): 105 mm

Abrasive paper width (hook and loop): 115 mm

Abrasive paper length (clamped): 140 mm

Abrasive paper width (clamped): 115 mm

Orbital stroke: 1.6 mm

Technical description

Abrasive paper width (clamped)	115 mm
maximum vibration to EN	< 8.5 m/s ²
Weight	1.6 kg
Abrasive paper mounting hook and loop	yes
Abrasive paper length (clamped)	140 mm
Abrasive paper mounting clamped	yes
Power consumption	260 W
Abrasive paper length (hook and loop)	105 mm
Orbital stroke	1.6 mm
Manufacturer's designation	SPS140
Speed of oscillation	28000 min ⁻¹
Abrasive paper width (hook and loop)	115 mm
Hole pattern	10-hole
Power supply	Mains-powered
Packaging	Carrying case
Type of product	Orbital sander

Accessories

Economy roll of abrasive cloth (A) robust, highly flexible Grit 80	556980 80
Abrasive paper pack, 10 pieces 10 holes Grit 60	557620 60
Economy roll of abrasive cloth (A) robust, highly flexible Grit 150	556980 150
Abrasive paper pack, 10 pieces 10 holes Grit 240	557620 240
Economy roll of abrasive cloth (A) robust, highly flexible Grit 240	556980 240
Economy roll of abrasive cloth (A) robust, highly flexible Grit 400	556980 400
	556980 600

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 600

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 60

556980 60

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 40

556980 40

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 320

556980 320

Abrasive paper pack, 10 pieces 10 holes Grit 120

557620 120

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 100

556980 100

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 120

556980 120

Economy roll of abrasive cloth (A) robust, highly flexible
Grit 180

556980 180

Abrasive paper pack, 10 pieces 10 holes Grit 80

557620 80