#### Garant GRIDUNG

# Drawer casing, 24G mobile, 20×20G, Casing height / number of drawers: 500/5mm



#### **Order data**

Order number	927620 500/5
GTIN	4062406124571
Item class	9GG

### **Description**

#### **Version:**

24G drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten.

Covering with a ribbed rubber mat, raised edge and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields.

Drawers with **individual drawer release system** prevents the opening of drawers during transport. Can be locked centrally with cylinder lock.

#### Fitted with:

Drawer front height, mm: 50, 75, 75, 100, 125

#### **Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable**, **always RAL 7035 light grey**.

#### Note:

Do not push these under workstations with electric height adjustment No. 920301 – 920316.

# **Technical description**

maximum load capacity	600 kg
Drawer body width	600 mm
Drawer runner extension (partial/full extension)	100 %
Drawer usable width	500 mm
Drawer usable width in G	20
Width	620 mm
Load capacity of upper shelf	50 kg
Weight	72 kg
Usable height	425 mm
Drawer body height	500 mm
Depth	740 mm
Individual drawer release system	One-hand
Drawer usable area in G	20×20
Drawer body depth	650 mm
Drawer usable depth in G	20
ComfortClose	no
Treadless tyres	yes
Number of fixed wheels without parking brake	2
Drawer usable depth	500 mm
Drawer/pull-out shelf load capacity	75 kg
Height	700 mm
Drawer body usable height	425 mm
Number of doors	0
Electronic locking system can be retrofitted	yes
with anti-roll lip	yes
Number of drawers	5
Number of castors with parking brake	2
Version	wheeled



Version	with drawers
Casing open at the top	no
Number of pull-out shelves	0
Usable height for drawers	425 mm
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workshop mobile drawer unit

## **Accessories**

Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927805 100
Drawer with one-handed individual drawer release system Drawer front height 50 mm	927805 50
Drawer with one-handed individual drawer release system Drawer front height 125 mm	927805 125
One-hand individual drawer release system Drawer usable width in G 20	951020 20
24G casing, mobile, for individual configuration with drawers Height of the housing 500 mm	927730 500
Lock plate for GridLine Type KO21	914227 KO21