

Garant GRIDLINE

**Drawer casing, 24G mobile, 20×20G, Casing height / number of drawers:
600/4mm****Order data**

Order number	927620 600/4
GTIN	4062406124588
Item class	9GG

Description**Version:**

24G drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten.

Covering with a ribbed rubber mat, raised edge and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields.

Drawers with **individual drawer release system** prevents the opening of drawers during transport. Can be locked centrally with cylinder lock.

Fitted with:

Drawer front height, mm: 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Do not push these under workstations with electric height adjustment No. 920301 – 920316.

Technical description

Drawer usable depth	500 mm
Number of doors	0
Drawer runner extension (partial/full extension)	100 %
Width	620 mm
Drawer usable width	500 mm
Drawer/pull-out shelf load capacity	75 kg
ComfortClose	no
Treadless tyres	yes
Drawer body height	600 mm
Height	800 mm
Drawer usable width in G	20
Load capacity of upper shelf	50 kg
Weight	69 kg
with anti-roll lip	yes
Usable height	525 mm
Drawer body usable height	525 mm
maximum load capacity	600 kg
Number of castors with parking brake	2
Drawer usable area in G	20×20
Drawer body depth	650 mm
Drawer usable depth in G	20
Drawer body width	600 mm
Electronic locking system can be retrofitted	yes
Number of fixed wheels without parking brake	2
Individual drawer release system	One-hand
Number of drawers	4
Depth	740 mm
Version	wheeled

Version	with drawers
Casing open at the top	no
Number of pull-out shelves	0
Usable height for drawers	525 mm
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workshop mobile drawer unit

Accessories

Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927805 100
Drawer with one-handed individual drawer release system Drawer front height 150 mm	927805 150
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Drawer with one-handed individual drawer release system Drawer front height 200 mm	927805 200
24G casing, mobile, for individual configuration with drawers Height of the housing 600 mm	927730 600
Lock plate for GridLine Type KO21	914227 KO21