

Garant GRIDLINE

**Drawer casing, 24G mobile, 20×20G, Casing height / number of drawers:
700/5mm****Order data**

Order number	927620 700/5
GTIN	4062406124595
Item class	9GG

Description**Version:**

24G drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten.

Covering with a ribbed rubber mat, raised edge and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields.

Drawers with **individual drawer release system** prevents the opening of drawers during transport. Can be locked centrally with cylinder lock.

Fitted with:

Drawer front height, mm: 75, 75, 100, 125, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Do not push these under workstations with electric height adjustment No. 920301 – 920316.

Technical description

Drawer runner extension (partial/full extension)	100 %
Treadless tyres	yes
Drawer usable depth in G	20
Drawer/pull-out shelf load capacity	75 kg
Depth	740 mm
Drawer usable area in G	20×20
Number of drawers	5
Height	900 mm
Drawer usable depth	500 mm
maximum load capacity	600 kg
with anti-roll lip	yes
Drawer body usable height	625 mm
Drawer body width	600 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Drawer body depth	650 mm
Number of doors	0
Width	620 mm
Number of fixed wheels without parking brake	2
Weight	80 kg
Drawer usable width in G	20
Load capacity of upper shelf	50 kg
Drawer usable width	500 mm
Drawer body height	700 mm
Individual drawer release system	One-hand
Number of castors with parking brake	2
Usable height	625 mm
Version	wheeled

Version	with drawers
Usable height for drawers	625 mm
Number of pull-out shelves	0
Casing open at the top	no
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workshop mobile drawer unit

Accessories

Drawer with one-handed individual drawer release system Drawer front height 125 mm	927805 125
Drawer with one-handed individual drawer release system Drawer front height 75 mm	927805 75
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Drawer with one-handed individual drawer release system Drawer front height 250 mm	927805 250
Drawer with one-handed individual drawer release system Drawer front height 100 mm	927805 100
24G casing, mobile, for individual configuration with drawers Height of the housing 700 mm	927730 700
Lock plate for GridLine Type KO21	914227 KO21