

## Garant

### Metal band saw blade 27×2750, TPI: 8/12



#### Order data

Order number	173597 8/12
GTIN	4062406124755
Item class	11S

#### Description

##### Version:

**GARANT** – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

##### Application:

**Variable pitch teeth 0°** – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

**Variable pitch teeth 10°** – **general purpose** for a wide range of cross-sections (for solid material from 50 mm).

**Regular pitch teeth 0°** – for small to medium cross-sections up to maximum 70 mm engagement length.

**Regular pitch teeth 10°** – for large cross-sections from 50 mm engagement.

##### Note:

**Running in a new blade:** See GARANT machining handbook No. 110010 and information page.

#### Technical description

Width	27 mm
Length	2750 mm

Thickness	0.9 mm
Tooth type	combi
Rake	0°
Tool material	HSS Co 8
Type of product	Metal band saw blade