

Garant**Metal band saw blade 27×2910, TPI: 8/12****Order data**

| | |
|--------------|---------------|
| Order number | 173657 8/12 |
| GTIN | 4062406125004 |
| Item class | 11S |

Description**Version:**

GARANT – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

Application:

Variable pitch teeth 0° – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

Variable pitch teeth 10° – **general purpose** for a wide range of cross-sections (for solid material from 50 mm).

Regular pitch teeth 0° – for small to medium cross-sections up to maximum 70 mm engagement length.

Regular pitch teeth 10° – for large cross-sections from 50 mm engagement.

Note:

Running in a new blade: See GARANT machining handbook No. 110010 and information page.

Technical description

| | |
|--------|---------|
| Width | 27 mm |
| Length | 2910 mm |

| | |
|-----------------|----------------------|
| Thickness | 0.9 mm |
| Rake | 0° |
| Tooth type | combi |
| Tool material | HSS Co 8 |
| Type of product | Metal band saw blade |