

Garant
Metal band saw blade 27×2835, TPI: 5/8

Order data

| | |
|--------------|---------------|
| Order number | 173627 5/8 |
| GTIN | 4062406124786 |
| Item class | 11S |

Description
Version:

GARANT – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

Application:

Variable pitch teeth 0° – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

Variable pitch teeth 10° – general purpose for a wide range of cross-sections (for solid material from 50 mm).

Regular pitch teeth 0° – for small to medium cross-sections up to maximum 70 mm engagement length.

Regular pitch teeth 10° – for large cross-sections from 50 mm engagement.

Note:

Running in a new blade: See GARANT machining handbook No. 110010 and information page.

Technical description

| | |
|--------|---------|
| Width | 27 mm |
| Length | 2835 mm |

| | |
|-----------------|----------------------|
| Thickness | 0.9 mm |
| Tooth type | combi |
| Rake | 0° |
| Tool material | HSS Co 8 |
| Type of product | Metal band saw blade |