

**Garant**
**Metal band saw blade 27×2835, TPI: 6/10**

**Order data**

Order number	173627 6/10
GTIN	4062406124793
Item class	11S

**Description**
**Version:**

**GARANT** – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

**Application:**

**Variable pitch teeth 0°** – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

**Variable pitch teeth 10°** – **general purpose** for a wide range of cross-sections (for solid material from 50 mm).

**Regular pitch teeth 0°** – for small to medium cross-sections up to maximum 70 mm engagement length.

**Regular pitch teeth 10°** – for large cross-sections from 50 mm engagement.

**Note:**

**Running in a new blade:** See GARANT machining handbook No. 110010 and information page.

**Technical description**

Thickness	0.9 mm
Width	27 mm

Length	2835 mm
Rake	0°
Tooth type	combi
Tool material	HSS Co 8
Type of product	Metal band saw blade