

Garant

Metal band saw blade 34×4150, TPI: 4/6H



Order data

Order number	173849 4/6H
GTIN	4062406124991
Item class	11S

Description

Version:

GARANT – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

Application:

Variable pitch teeth 0° – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

Variable pitch teeth 10° – **general purpose** for a wide range of cross-sections (for solid material from 50 mm).

Regular pitch teeth 0° – for small to medium cross-sections up to maximum 70 mm engagement length.

Regular pitch teeth 10° – for large cross-sections from 50 mm engagement.

Note:

Running in a new blade: See GARANT machining handbook No. 110010 and information page.

Technical description

Width	34 mm
Length	4150 mm

Thickness	1.1 mm
Rake	10 °
Tooth type	combi
Tool material	HSS Co 8
Type of product	Metal band saw blade