

**Garant**
**Metal band saw blade 34×4530, TPI: 3/4H**

**Order data**

Order number	173853 3/4H
GTIN	4062406125073
Item class	11S

**Description**
**Version:**

**GARANT** – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

**Application:**

**Variable pitch teeth 0°** – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

**Variable pitch teeth 10°** – **general purpose** for a wide range of cross-sections (for solid material from 50 mm).

**Regular pitch teeth 0°** – for small to medium cross-sections up to maximum 70 mm engagement length.

**Regular pitch teeth 10°** – for large cross-sections from 50 mm engagement.

**Note:**

**Running in a new blade:** See GARANT machining handbook No. 110010 and information page.

**Technical description**

Width	34 mm
Thickness	1.1 mm

Length	4530 mm
Tooth type	combi
Rake	10°
Tool material	HSS Co 8
Type of product	Metal band saw blade