

Garant
Metal band saw blade 34×5090, TPI: 2/3H

Order data

Order number	173865 2/3H
GTIN	4062406125394
Item class	11S

Description
Version:

GARANT – high-performance bi-metal band saw blade with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

Application:

Variable pitch teeth 0° – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

Variable pitch teeth 10° – **general purpose** for a wide range of cross-sections (for solid material from 50 mm).

Regular pitch teeth 0° – for small to medium cross-sections up to maximum 70 mm engagement length.

Regular pitch teeth 10° – for large cross-sections from 50 mm engagement.

Note:

Running in a new blade: See GARANT machining handbook No. 110010 and information page.

Technical description

Length	5090 mm
Thickness	1.1 mm

Width	34 mm
Tooth type	combi
Rake	10°
Tool material	HSS Co 8
Type of product	Metal band saw blade