

## Garant

### Metal band saw blade 27×4150, TPI: 3/4H



#### Order data

Order number	173837 3/4H
GTIN	4062406125349
Item class	11S

#### Description

##### Version:

**GARANT – high-performance bi-metal band saw blade** with wear-resistant **M42 teeth** and special flexible backing with increased load capacity.

##### Application:

**Variable pitch teeth 0°** – very low vibration, for a large range of cross sections (for pipes and profiles, solid materials up to maximum 70 mm).

**Variable pitch teeth 10° – general purpose** for a wide range of cross-sections (for solid material from 50 mm).

**Regular pitch teeth 0°** – for small to medium cross-sections up to maximum 70 mm engagement length.

**Regular pitch teeth 10°** – for large cross-sections from 50 mm engagement.

##### Note:

**Running in a new blade:** See GARANT machining handbook No. 110010 and information page.

#### Technical description

Width	27 mm
Thickness	0.9 mm

Length	4150 mm
Tooth type	combi
Rake	10°
Tool material	HSS Co 8
Type of product	Metal band saw blade