

Garant

Digital caliper IP67 with data output including a set of accessories, Measuring range: 150mm



Order data

Order number	412845 150
GTIN	4062406127374
Item class	41A

Description

Version:

Digital caliper with comprehensive accessories - **permits measurement of recesses, slots and hole pitches.**

- **Easy-to-read, high-contrast LCD display with 11.5 mm character height.**
- **Very long battery running time due to modern energy-efficient measurement system.**
- **Ergonomic housing with easy-grip Haptoprene component.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

- 1× **IP67** digital caliper with data output No. 412690 size 150.
 - 1 battery No. 081560 size CR2032.
 - 2 pairs of contact point carriers short and long.
 - 3 pairs of measuring tips with measuring discs Ø 6 mm, Ø 10 mm, Ø 12.5 mm.
 - 2 pairs of measuring tips with anvil cones Ø 9 mm, 60° and Ø 12 mm, 60°.
 - 1 pair of measuring tips with measuring cylinders Ø 1.5×9 mm.
 - 1× spring system for constant gauging force.
 - 1× hexagon key L-wrench.
 - 1× depth extension base 75 mm.
- Supplied in a sturdy plastic box.

Spare part:

Data output cap No. 412237 size D, battery holder No. 412237 size B.

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Standard	ISO 13385
Calibration	A1
Scale divisions	0.01 mm
Reversible reading	mm / inch
Depth gauge	rectangular 3.7×1.3
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Jaw length	40 mm
Number of batteries contained	1
Depth gauge available	yes
Digit height LCD display	11.5 mm
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	±0.02 mm
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum
measuring range 200 mm

021010 200

021000 200

CalibrationCalipers / depth gauges maximum measuring range 200 mm

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------

Digital caliperIP67 with data output Measuring range 150 mm	412690 150
---	------------

Screw for depth gauge holder	412236
------------------------------	--------

Cover for digital calipers Type B	412237 B
-----------------------------------	----------