



JOKER 6000 open ended spanners / ratchet ring spanners, imperial, Width across flats: 3/8in



Order data

Order number	614890 3/8
GTIN	4013288167361
Item class	63F

Description

Version:

Drop forged. Ring end with smooth-running sturdy precision ring ratchet (80 teeth) with a particularly small working arc of 4.5°.

The open end has a bi-hexagon profile and a replaceable hardened metal plate, which fulfils a stop function, preventing slippage and allowing a small working arc.

Material:

Chrome molybdenum steel, matt chrome-plated.

Spanner length L: 159 mm

Jaw width b: 22 mm

Jaw height h_1 : 5.5 mm

Ring thickness h_2 : 7.2 mm

Ring \varnothing D: 21 mm

Technical description

Ring thickness h_2	7.2 mm
Ring \varnothing D	21 mm
Width across flats	3/8 in
Jaw width b	22 mm
Spanner length L	159 mm
Jaw height h_1	5.5 mm
Width across flats	imperial

Manufacturer's designation	6000 Joker Imperial
Ring setting	0 °
No. of teeth	80
Working arc	4.5 °
Manufacturing process	drop forged
Material	Chrome-molybdenum steel.
Surface	matt chrome-plated
Ratchet reversible	no
Type of product	Spanner