



WD-40® multi-function product Flexible, Contents: 400ml



Order data

Order number	083003 400
GTIN	5032227316881
Item class	08E

Description

Version:

WD-40 multi-function oil is proven world-wide, **almost completely odourless, uses non-polluting propellant**, is Teflon, resin, silicone, and acid-free.

Application:

- **Rust remover with penetrating capillary action – quickly releases seized bolts and nuts.**
- **Cleaner – loosens stubborn dirt, without sticking or gumming up.**
- **Lubricant for all sliding surfaces, precision mechanics, hinges, Bowden cables, locks and catches.**
- **Corrosion protection – WD-40 penetrates under moisture and into the pores of the material to be protected, thus preserving it. Delicate and expensive tools retain their value.**
- **Contact spray – displaces moisture from electrical components.**

With flexible metal spray tube 18.5 cm for precise application. Can be used at all angles of inclination.

Note:

Approved by: **Rolls Royce, Daimler, Airbus, VW** amongst others.
Not available in all countries. Express delivery not available.

Technical description

Spray head	Flexi Straw
Labelling of hazardous substances	GHS07: Exclamation mark
Labelling of hazardous substances	GHS02: Flame
Colour	pale brown
hazardous goods class	2.1
Flashpoint	47 °C
Boiling point	176 °C
Oxidisation characteristics	no
Solubility in water	insoluble
Kinematic viscosity	< 1 mm ² /s
Storage temperature	15 - 50 °C
Contents	0.4 l
Version	Spray can
Type of product	Multi-function oil / universal oil