



JOKER 6000 open ended spanners / ratchet ring spanners, imperial, Width across flats: 11/16in



Order data

Order number	614890 11/16
GTIN	4013288167439
Item class	63F

Description

Version:

Drop forged. Ring end with smooth-running sturdy precision ring ratchet (80 teeth) with a particularly small working arc of 4.5°.

The open end has a bi-hexagon profile and a replaceable hardened metal plate, which fulfils a stop function, preventing slippage and allowing a small working arc.

Material:

Chrome molybdenum steel, matt chrome-plated.

Spanner length L: 235 mm

Jaw width b: 39 mm

Jaw height h_1 : 9 mm

Ring thickness h_2 : 11 mm

Ring \varnothing D: 33.8 mm

Technical description

Spanner length L	235 mm
Ring thickness h_2	11 mm
Ring \varnothing D	33.8 mm
Jaw width b	39 mm
Width across flats	11/16 in
Jaw height h_1	9 mm
Width across flats	imperial

Manufacturer's designation	6000 Joker Imperial
Ring setting	0 °
No. of teeth	80
Working arc	4.5 °
Manufacturing process	drop forged
Material	Chrome-molybdenum steel.
Surface	matt chrome-plated
Ratchet reversible	no
Type of product	Spanner