

Garant**LED rechargeable battery torch, Type: 145mm****Order data**

Order number	081545 145
GTIN	4045197727244
Item class	01A

Description**Version:**

Focussable and very sturdy LED torch of anodised aluminium. The single-hand focussing enables quick and easy adjustment of the beam. Rotary switch with integral charging status display and micro-USB port.

Supplied with:

Supplied with a micro-USB charger, hand loop and GARANT transport box.

Torch function: Focus

ATEX zone: no

Illumination: 300 lm

Working life: 3 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Overall length: 145 mm

Technical description

Illumination	300 lm
Battery capacity	2.6 A·h
Weight	188 g
Head Ø	35 mm
Working life	3 h
ATEX zone	no
Number of rechargeable batteries contained	1

Torch function	Focus
Overall length	145 mm
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Flashlight

Accessories

USB charger plug Type MICRO-USB	081591 MICRO-USB
---------------------------------	------------------