



## JOKER 6000 open ended spanners / ratchet ring spanners, imperial, Width across flats: 5/16in



### Order data

Order number	614890 5/16
GTIN	4013288167354
Item class	63F

### Description

#### Version:

Drop forged. Ring end with smooth-running sturdy precision ring ratchet (80 teeth) with a particularly small working arc of 4.5°.

The open end has a bi-hexagon profile and a replaceable hardened metal plate, which fulfils a stop function, preventing slippage and allowing a small working arc.

#### Material:

Chrome molybdenum steel, matt chrome-plated.

Spanner length L: 144 mm

Jaw width b: 20 mm

Jaw height  $h_1$ : 5.5 mm

Ring thickness  $h_2$ : 7 mm

Ring  $\varnothing$  D: 18 mm

### Technical description

Jaw width b	20 mm
Ring $\varnothing$ D	18 mm
Ring thickness $h_2$	7 mm
Jaw height $h_1$	5.5 mm
Spanner length L	144 mm
Width across flats	5/16 in
Width across flats	imperial

Manufacturer's designation	6000 Joker Imperial
Ring setting	0 °
No. of teeth	80
Working arc	4.5 °
Manufacturing process	drop forged
Material	Chrome-molybdenum steel.
Surface	matt chrome-plated
Ratchet reversible	no
Type of product	Spanner