

Garant**Boring bar carbide elliptical, right-hand, Shank \varnothing DS / overhang L1: 16/64mm****Order data**

Order number	273969 16/64
GTIN	4062406128050
Item class	21U

Description**Version:**

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to handle.**

Elliptical profile for very high flexional resistance.

Low-vibration carbide shank with soldered steel head and hardened insert seat.

Technical description

Insert screw	279810 1
Overall length L	130 mm
Overhang L ₁ recessed holders	64 mm
Clamping height L ₂	15 mm
Shank \varnothing D _s	16 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	yes
Type of product	Boring bar