

Garant**Boring bar carbide elliptical, right-hand, Shank Ø DS / overhang L1: 12/45mm****Order data**

Order number	273969 12/45
GTIN	4062406128012
Item class	21U

Description**Version:**

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to handle.**

Elliptical profile for very high flexional resistance.

Low-vibration carbide shank with soldered steel head and hardened insert seat.

Technical description

Overall length L	110 mm
Insert screw	279810 1
Overhang L ₁ recessed holders	45 mm
Clamping height L ₂	11 mm
Shank Ø D _s	12 mm
Application range	axial external grooving
Application type	right-hand
Through-coolant	yes
axial grooving possible	yes
Type of product	Boring bar

