

Garant**Boring bar steel, right-hand, Shank Ø DS / overhang L1: 12/20mm****Order data**

Order number	273963 12/20
GTIN	4062406128128
Item class	21U

Description**Version:**

- Carbide insert screwed on to the end face, positive force transmission due to end face serrations.
- Insert change is very easy to handle.

Technical description

Overall length L	78 mm
Insert screw	279810 1
Overhang L ₁ recessed holders	20 mm
Clamping height L ₂	11 mm
Shank Ø D _s	12 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	yes
Type of product	Boring bar