

Garant**Boring bar carbide round, right-hand, Shank \varnothing DS / overhang L1: 12/34mm**

Order data

Order number	273966 12/34
GTIN	4062406128074
Item class	21U

Description

Version:

- **Carbide insert screwed on to the end face, positive force transmission due to end face serrations.**
- **Insert change is very easy to handle.**

Low-vibration carbide shank with soldered steel head and hardened insert seat.

Technical description

Overall length L	100 mm
Insert screw	279810 1
Overhang L ₁ recessed holders	34 mm
Clamping height L ₂	11 mm
Shank \varnothing D _s	12 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	yes
Type of product	Boring bar