



JOKER 6000 open ended spanners / ratchet ring spanners, imperial, Width across flats: 1/2in



Order data

Order number	614890 1/2
GTIN	4013288167385
Item class	63F

Description

Version:

Drop forged. Ring end with smooth-running sturdy precision ring ratchet (80 teeth) with a particularly small working arc of 4.5°.

The open end has a bi-hexagon profile and a replaceable hardened metal plate, which fulfils a stop function, preventing slippage and allowing a small working arc.

Material:

Chrome molybdenum steel, matt chrome-plated.

Spanner length L: 177 mm

Jaw width b: 27.3 mm

Jaw height h_1 : 7 mm

Ring thickness h_2 : 8.6 mm

Ring \varnothing D: 25 mm

Technical description

Spanner length L	177 mm
Jaw height h_1	7 mm
Jaw width b	27.3 mm
Width across flats	1/2 in
Ring \varnothing D	25 mm
Ring thickness h_2	8.6 mm
Width across flats	imperial

Manufacturer's designation	6000 Joker Imperial
Ring setting	0 °
No. of teeth	80
Working arc	4.5 °
Manufacturing process	drop forged
Material	Chrome-molybdenum steel.
Surface	matt chrome-plated
Ratchet reversible	no
Type of product	Spanner