

Garant**Rigid foam holder, Type: 2****Order data**

Order number	956820 2
GTIN	4062406127602
Item class	91F

Description**Version:**

Rigid foam holder of sheet metal to take rigid foam inlays of 20G / 500 mm width. With facility for an additional central restraint to secure two foam inlays. Each holder can take 2 rigid foam inlays of size 8×20G or 4 foam inlays of size 8×10G.

Suitable for:

For hanging up in perforated panels □ 9×9 mm in 37 mm grid.
Can also be attached to the worktop with 4 wood screws (not included).

Colour:

Rigid foam holder RAL 7035 light grey, additional holder RAL 7016 anthracite, **powder-coated**.

Note:

Suitable only for foam inlays in which the tools lie virtually flush.
Only limited suitability for the foam inlays listed in the catalogue. Tools must be planned for a close fit in an individually configured foam inlay.

Technical description

Usable height	400 mm
Width	500 mm

Depth	125 mm
Type	2
suitable for foam thickness	45 mm
Usable width	500 mm
Height	440 mm
Type of product	Rigid foam holder