

Mitutoyo
Digital height gauge QM-Height, Type: 350

Order data

Order number	445233 350
GTIN	4946368760568
Item class	44B

Description
Version:

High-accuracy compact height gauge with manual adjustment and easy-to-read monochrome LCD display. Many measurement and analysis functions for data processing. Quick and easy selection of functions and all leading calculations of internal and external diameters, as well as distances. Unlimited speed of positioning. Improved battery life.

Application:

Ideal for the workshop and inspection room.

Supplied with:

Supplied with ball contact point 5 mm Ø, calibration block, 4 batteries No. 081561 size LR6.

Optional extras:

Contact point, marking out scriber, data cable and mains adaptor.

Technical description

Graduations can be switched over	0.001 / 0.0005 mm
Measurement slide movement	manual
Error limit (L = meas. length in mm)	$2.4 + 3.5 L / 1000 \mu\text{m}$

Gauging force	1.5 ±0.5 N
Number of batteries contained	4
Calibration	E2
Rectangularity error (frontal)	7 µm
Repeatability plane	1.8 µm
Article no of the battery / rechargeable battery fitted	081560 LR6
maximum application range	0 - 465 mm
Measuring range	0 - 350 mm
Power supply	Battery-powered
Power supply	Mains operated
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Type of product	Height gauge

Services

CalibrationDigital height gauge maximum measuring range 400 mm	024000 400
DAkkS calibrationDigital height gauge maximum measuring range 400 mm	024010 400

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------