

Mitutoyo**Digital height gauge QM-Height with air pad, Type: 600****Order data**

Order number	445234 600
GTIN	4946368760629
Item class	44B

Description**Version:**

High-accuracy compact height gauge with manual adjustment and easy-to-read monochrome LCD display. Many measurement and analysis functions for data processing. Quick and easy selection of functions and all leading calculations of internal and external diameters, as well as distances. Unlimited speed of positioning. Improved battery life.

Air pad for easy, jerk-free movement.**Application:**

Ideal for the workshop and inspection room.

Supplied with:

Supplied with ball contact point 5 mm Ø, calibration block, 4 batteries No. 081561 size LR6.

Optional extras:

Contact point, marking out scriber, data cable and mains adaptor.

Technical description

Graduations can be switched over	0.001 / 0.0005 mm
Number of batteries contained	4
Rectangularity error (frontal)	12 µm

Measuring range	0 - 600 mm
Repeatability plane	1.8 µm
Calibration	E2
Error limit (L = meas. length in mm)	2.4 + 3.5 L / 1000 µm
Gauging force	1.5 ±0.5 N
Measurement slide movement	manual
maximum application range	0 - 715 mm
Article no of the battery / rechargeable battery fitted	081560 LR6
Power supply	Battery-powered
Power supply	Mains operated
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Type of product	Height gauge

Services

CalibrationDigital height gauge maximum measuring range 800 mm	024000 800
DAkkS calibrationDigital height gauge maximum measuring range 800 mm	024010 800