

**LED rechargeable work lamp, Type: MAG****Order data**

Order number	081516 MAG
GTIN	5708997354001
Item class	08C

Description**Version:**

LED rechargeable work lamp with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet.

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Supplied with:

Supplied with USB charging cable.

Technical description

Illumination	300 - 500 lm
Battery voltage	3.7 V
Power supply	Rechargeable battery powered
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Bulb	LED module

Battery capacity	2.2 Ah
Illumination step 2	150 lm
Illumination time	2.5 h
Overall length	260 mm
Illumination time stage 2	5 h
IP Index of Protection	IP 20
Overall width	61 mm
Weight	273 g
ATEX zone	no
Manufacturer's designation	MAG
Type of product	Work lamp

Accessories

USB charger Type CABLE	081512 CABLE
------------------------	--------------