



LED rechargeable work light, Type: MINIFORM



Order data

Order number	081516 MINIFORM
GTIN	5708997354049
Item class	08C

Description

Version:

LED rechargeable work light with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. **Miniform** version, **slim**, handy size for the pocket (120×59×25 mm), belt clip, ergonomic handle.

High-performance **COB LED technology for extremely bright homogeneous lighting of an area at two levels of brightness.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB charging cable.

Technical description

Illumination	200 lm
Number of rechargeable batteries contained	1
Bulb	LED module
Power supply	Rechargeable battery powered

Illumination step 2	100 lm
Type of rechargeable battery	Lithium-ion
Battery voltage	3.7 V
Battery capacity	1.6 Ah
Overall width	59 mm
Illumination time	2.5 h
Overall length	120 mm
Illumination time stage 2	5 h
IP Index of Protection	IP 65
Weight	138 g
ATEX zone	no
Manufacturer's designation	MINIFORM
Type of product	Work lamp