

**LED rechargeable work light, Type: 205****Order data**

Order number	081537 205
GTIN	4045197727251
Item class	02A

Description**Version:**

LED rechargeable work lamp with 2 brightness levels and high illumination intensity. With suspension hook and fold-down support, **micro-USB charging port**, rotating magnetic base and hand loop.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with charging cable and plug-in power supply unit.

Technical description

Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery powered
Battery voltage	3.7 V
Number of rechargeable batteries contained	1

Illumination step 2	250 lm
Illumination	350 lm
Illumination time	3.5 - 5.5 h
IP Index of Protection	IP 65
Overall length	205 mm
Weight	266 g
ATEX zone	no
Type of product	Work lamp