

**Diamond sheet, Grit: D64µm****Order data**

Order number	529112 D64
GTIN	4007220955918
Item class	53B

Description**Version:**

Flexible diamond sheet, coated **on both sides** with abrasive diamond grit. Height including grit 0.7 mm.

Application:

Ideal for grinding work on concave and convex surfaces.

Note:

Diamond files can be cleaned in petrol with a metal brush (e.g. 576000).

Technical description

Grit designation	fine
Grit	D64
Dimensions	35×350 mm
Grinding media	Diamond
Grinding medium code	D
Width	35 mm
Height	0.7 mm
Length	350 mm
Type of product	Diamond file

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Stone	suitable only under restricted conditions		