

**Instant adhesive, 20 g, Type: SLOW****Order data**

Order number	083361 SLOW
GTIN	4062406127886
Item class	02A

Description**Version:**

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity. Slow-curing, high-strength and gap filling ability, suitable for **metal and hard plastics** and **all absorbent surfaces/materials** such as **leather, wood, cork**.

Note:

Not available in all countries. Express delivery not available.

Technical description

Labelling of hazardous substances	GHS07: Exclamation mark
Touch dry after	20 - 50 s
Tensile shear strength	10 - 22 N/mm ²
Dynamic viscosity	600 - 1500 mPas
Storage temperature	20 °C
Working life after date of manufacture	9 mo

Characteristics	does not penetrate into workpiece surface
Operating temperature range	-55 °C
Tensile strength	10 - 20 N/mm ²
Density	1.06 g/cm ³
Chemical basis	Ethyl cyanoacrylate
Colour	transparent
Shape	liquid
Suitable for material	Leather
Suitable for material	wood
Suitable for material	Metal
Suitable for material	Cork
Suitable for material	porous materials
Suitable for material	Rubber
Suitable for material	Plastic
Capacity	20 ml
Product name attribute	20 g
Type of product	Instant adhesive