

Garant**Toolholder for imperial profile broaching tools $\varnothing d = 8$ mm, Shank $\varnothing DS: 1$ in**

Order data

| | |
|--------------|---------------|
| Order number | 293070 1 |
| GTIN | 4062406128999 |
| Item class | 29K |

Description

Suitable for:

CNC and conventional machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MK2, MK3 and MK4.

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

| | |
|--------------------|-------------|
| Shank length L_s | 50 mm |
| L | 38 mm |
| Shank type | Plain shank |
| $\varnothing D$ | 33 mm |
| $\varnothing d$ | 8 mm |

| | |
|-----------------|--|
| Shank size | 1 in |
| Through-coolant | no |
| Type of product | Keyway broaching and profile slotting tool |

Accessories

| | |
|--------------------------------|-----------|
| Pin spanner for holder Ø 16 mm | 293006 16 |
| Pin spanner for holder Ø 5 mm | 293006 5 |
| Pin spanner for holder Ø 12 mm | 293006 12 |
| Pin spanner for holder Ø 8 mm | 293006 8 |