

Garant**Toolholder for imperial profile broaching tools $\varnothing d = 5$ mm, Shank $\varnothing DS: 5/8$ in****Order data**

Order number	293079 5/8
GTIN	4062406128951
Item class	29K

Description**Version:**

Suitable for automatic lathes.

Suitable for:

CNC and conventional machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MK2, MK3 and MK4.

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

L	34 mm
Shank length L_s	35 mm
Shank type	Plain shank
$\varnothing D$	22 mm

Ø d	5 mm
Shank size	5/8 in
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

Accessories

Pin spanner for holder Ø 5 mm	293006 5
Pin spanner for holder Ø 8 mm	293006 8
Pin spanner for holder Ø 12 mm	293006 12
Pin spanner for holder Ø 16 mm	293006 16